



Material	103646E
Material description	N,N-Dimethylacetamide
Grade	AnalaR NORMAPUR
CAS Number	127-19-5
Molecular formula	C ₄ H ₉ NO
Molecular mass	87.12

Characteristics	Specifications
Assay	Min. 99.5 %
Insolubility in water	Passes test
IR Spectrum	Passes test
Acidity	Max. 0.02 meq/g
Colouration	Max. 10 APHA
Non-volatile residue	Max. 100 ppm
Water	Max. 0.1 %
Cl (Chloride)	Max. 10 ppm
SO ₄ (Sulphate)	Max. 10 ppm
Cu (Copper)	Max. 1 ppm
Fe (Iron)	Max. 1 ppm
Pb (Lead)	Max. 1 ppm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.