



Material	441476L
Material description	2-[4-(2-Hydroxyethyl)-1-piperazinyl]-ethanesulphonic acid
CAS Number	7365-45-9
Molecular formula	C ₈ H ₁₈ N ₂ O ₄ S
Molecular mass	238.30

Characteristics	Specifications
Assay	Min. 99.5 %
Cl (Chloride)	Max. 0.05 %
SO ₄ (Sulphate)	Max. 0.05 %
Heavy metals (as Pb)	Max. 10 ppm
pH (25°C; 1 %)	4.7 --> 6.0
Water	Max. 0.5 %

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

VWR International

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.