



Material	102454R
Material description	Sodium dihydrogen phosphate monohydrate
Grade	AnalaR NORMAPUR
CAS Number	10049-21-5
Molecular formula	H ₂ NaO ₄ P.H ₂ O
Molecular mass	137.99

Characteristics	Specifications
Assay	99.0 --> 102.0 %
Solution in water	Passes test
pH (5 %)	4.1 --> 4.5
Cl (Chloride)	Max. 0.0005 %
SO ₄ (Sulphate)	Max. 0.005 %
Total N (Nitrogen)	Max. 0.001 %
Heavy metals (as Pb)	Max. 0.0005 %
As (Arsenic)	Max. 0.00005 %
Ca (Calcium)	Max. 0.005 %
Cu (Copper)	Max. 0.0002 %
Fe (Iron)	Max. 0.0005 %
K (Potassium)	Max. 0.005 %
Pb (Lead)	Max. 0.0005 %

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

VWR International