



Certificate of Conformity

VWR MULTI CHANNEL PIPETTES, 8-CHANNELS, MECHANICAL,ULTRA HIGH PERFORMANCE

VWR International certifies that the products comply in every respect with the relevant particular specifications and/or drawings and/or relevant standards and regulations in force, mentioned in this document.

VWR International certifie que les produits sont conformes à tous égards aux spécifications particulières appropriées et / ou dessins, normes et règlements en vigueur, mentionnées dans le présent document

VWR International bestätigt, dass das Produkte allen zutreffenden Spezifikations- und/oder Zeichnungs- und/oder Standardanforderungen sowie den im Dokument aufgeführten gültigen Vorschriften entspricht.

VWR Cat.Number	Capacity (μ l)	Accuracy (%)	Imprecision (%)	Pk
613-1494	1 - 10	$\pm 8.0 - \pm 2.0$	<6.0 - <1.2	1
613-1495	5 - 50	$\pm 4.0 - \pm 1.6$	<2.5 - <0.6	1
613-1496	2 - 200	$3.0 - \pm 1.0$	<1.5 - <0.6	1
613-1497	50 - 300	$\pm 1.6 - \pm 1.0$	<1.5 - <0.6	1

The products pass stringent validation & control procedures based on EN ISO 8655. They are calibrated & tested using gravimetry method with distilled water.

The conditions of measurement : Basis of adjustment: Ex; reference temperature: 20°C; relative air humidity: 50%; Barometric pressure:101kpa.

Other Characteristics:

- The VWR Ultra-High Performance pipettes offer superior accuracy and precision, with proven ergonomic design both lightweight and durable.
- Low plunger forces
- Universal tip capability
- Automatic locking volume adjustment wheel
- Levered tip ejection and colour coded for volume identification
- Easy in-house calibration and maintenance

Disclaimer: VWR wants to state that this declaration will not discharge the user from his obligation to ensure the product is suitable for the intended use. - If there is any doubt ask us.

Date of issue: **September 2016**