



Material	332732B
Material description	Buffer pH 4,01 ± 0,02 (25°C) capsules
Grade	Reagent traceable to SRM from NIST

Characteristics	Specifications
pH (25°C)	3.99 --> 4.03

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

VWR International