

Material	351042L
Material description	HEMA 'GURR' rapid staining set for haematology for microscopy

## Characteristics

## Specifications

Absorption maximum solution 2	513 - 518 nm
Absorption maximum solution 3	630 - 652 nm
Absorbance solution 2 (l <sup>m</sup> ax; diluted 1	0.590 - 0.630
Absorbance solution 3 (l <sup>m</sup> ax; diluted 1	0.800 - 0.860
Suitability for microscopy (Blood smear)	passes test
Nuclei	red-violet
Erythrocytes	pink to brownish
Eosinophilic granules	red to red-brown
Neutrophilic granules	light violet
Lymphocyte cytoplasm	blue

## Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

VWR International

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.