

Product information

VWR[®] Tablet PC with Camera TC210

EU cat. no

630-2678



General specifications	USB output	Yes
	C-Mount	Yes
	Dimensions (mm)	58 x 58 x 36.4
	Weight (kg)	0.18

Sensor	Camera resolution (n° of pixels: W x H)	2592x1944
	Color / Monochrome	Color
	Sensor Size	1/2.5"
	Sensor Technology	CMOS
	Sensor Type	APTINA CMOS
	Image Format	4/3
	Pixel Size (mm)	2.2x2.2
	Acquisition technology	Rolling shutter
	Sensitivity	0.53 V/lux-second
	Signal/Noise Ratio (DB)	40.5
	Dynamic range (DB)	66.5
	ADC conversion	8 Bit
	Color Depth	1, 4, 8, 24 Bit
	Exposure time	0.294 msec - 2 sec
	Binning	1x1; 2x2; 4x4
	IR filter	Yes
	IR filter range (nm)	380-650 (IR CUT)

USB	PC Camera resolution (MP)	5.1
	USB standard	USB2.0
	Frame rate full resolution (fps)	7@2592x1944
	Frame rate other resolution (fps)	27@1280x960; 90@640x480

Camera Power Supply	Type	External
	Output voltage	PC USB

Camera accessories	Optical adapter (for 23mm eyepiece tube)	0.5x
	Calibration slide	Yes

Environment	Working Temperature	-10°C up to +50°C
	Storage Temperature	-20°C up to +60°C
	Relative Humidity	30% to 80%
	Storage Humidity	10% to 60%

Operating System	OS	Windows 10 (64Bit)
-------------------------	----	--------------------

Available Software	PC SW	PROVIEW
---------------------------	-------	---------

Tablet	Operating system	Windows 10 (64Bit)
	CPU	Intel® Celeron, N3350
	CPU speed	1.10 GHz
	Graphic card	Intel® HD Graphics 500
	RAM	Ram 6 GB DDR3
	Display size	LED 10.1" IPS Multi Touch Screen
	Display resolution	1920x1200
	Storage	Hdd 64 GB
	Network	802.11b/g/n/ac, 2.4GHz+5.0GHz
	Input ports	USB 3.0, Type C, Micro SD card reader, Microphone, DC in
	Output ports	Headphone - Micro HDMI

	Battery Type	Lithium-ion
	Battery capacity	3500 mAh
	Power consumption	24.05W
	Power supply	12V 2A EU / US
	Dimensions (mm)	247 x 165 X 9
	Weight (Kg)	0.57
	Language	Multilanguage

Tablet accessories	USB cable USB-B to USB-A (0.5m)	Yes
---------------------------	---------------------------------	-----