



Material	22707.364
Material description	Chloroform
Grade	GPR RECTAPUR Stabilized with 2-methyl-2-butene
CAS Number	67-66-3
Molecular formula	CHCl ₃
Molecular mass	119.38

Characteristics	Specifications
Assay	Min. 99 %
Boiling point	59.5 --> 61.5 °C
Density (20/4)	1.478 --> 1.489
Evaporation residue	Max. 10 ppm
Free chlorine	Max. 10 ppm
Heavy metals (as Pb)	Max. 10 ppm
Water	Max. 100 ppm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.