Product Specification

Material	83608.290
Material description	Conductivity standard 12,880 µS/cm (25°C; 0.1 mol/l; KCl)
Grade	calibration solution for conductibility
Molecular formula	ClK

Characteristics	Specifications
Titer	0.0990 --> 0.1100 mol/l
Conductivity (25°C)	12.60 --> 13.00 mS/cm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Anja Vanhalle, Head of Laboratory - Haasrode
VWR International bvba; Geldenaaksebaan 464; BE-3001 Leuven; Belgium

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.