Product Specification

Material	26930.293
Material description	di-Potassium hydrogen phosphate
Grade	GPR RECTAPUR
CAS Number	7758-11-4
Molecular formula	HK2O4P
Molecular mass	174.18

Characteristics	Specifications
Assay	Min. 97 %
Heavy metals (as Pb)	Max. 50 ppm
Cl (Chloride)	Max. 0.02 %
SO4 (Sulphate)	Max. 0.05 %
Fe (Iron)	Max. 50 ppm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Anja Vanhalle, Head of Laboratory - Haasrode
VWR International bvba; Geldenaaksebaan 464; BE-3001 Leuven; Belgium

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.