

Model:
SZB350 OH - 630-1583

Typology:
LABORATORY STEREOMICROSCOPE

Description:
Stereomicroscope for laboratory and industry applications.

Illumination	The microscope is not equipped with its own illumination, but it can use external illumination systems (halogen, LED, fiber guides).
Focusing	By means of a rack and pinion controlled by a pair of knobs placed on both sides of the stereomicroscope..
Stand	Overhanging stand, pillar height 42 cm. Horizontal arm 45 cm. Base: 23x23x6h cm. Weight: 15 Kg
Head	Binocular rotating 360° and 45° inclined. Diopter adjustment on both eyepieces. Interpupillary adjustment 51-75 mm.
Eyepieces	Widefield eyepieces WF10x/20 with field number 20.
Objectives	Parfocal achromatic objective 1X Working distance: 100 mm Zoom range: 0,7x - 4,5x Zoom factor: 6,428:1
Accessories	Instruction manual and dust cover included.