Product Specification

Material	102766H
Material description	Sulphuric acid 98%
Grade	AnalaR NORMAPUR
CAS Number	7664-93-9
Molecular formula	H2O4S
Molecular mass	98.07

Characteristics	Specifications
Assay	Min. 98.0 %
Colour	Max. 10 APHA
Cl (Chloride)	Max. 0.00002 %
NO3 (Nitrate)	Max. 0.00002 %
Al (Aluminium)	Max. 0.00001 %
As (Arsenic)	Max. 0.000005 %
Ba (Barium)	Max. 0.000005 %
Ca (Calcium)	Max. 0.0001 %
Cd (Cadmium)	Max. 0.000005 %
Co (Cobalt)	Max. 0.000002 %
Cr (Chromium)	Max. 0.00001 %
Cu (Copper)	Max. 0.000002 %
Fe (Iron)	Max. 0.0001 %
K (Potassium)	Max. 0.00005 %
Mg (Magnesium)	Max. 0.00005 %
Mn (Manganese)	Max. 0.000002 %
Mo (Molybdenum)	Max. 0.000005 %
NH4 (Ammonium)	Max. 0.0002 %
Na (Sodium)	Max. 0.0005 %
Ni (Nickel)	Max. 0.000005 %
Pb (Lead)	Max. 0.000005 %
Se (Selenium)	Max. 0.0001 %
Sr (Strontium)	Max. 0.000002 %
Zn (Zinc)	Max. 0.00005 %
Substances reducing KMnO4 (as O)	Max. 0.0001 %
Non-volatile matter	Max. 0.002 %

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.

Product Specification

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

VWR International