



Material	141976Y
Material description	White Spirit
Grade	SPECTRONORM
CAS Number	64742-48-9

Characteristics	Specifications
Density (20/4)	0.750 --> 0.790
Al (Aluminium)	Max. 0.02 ppm
Ba (Barium)	Max. 0.05 ppm
Ca (Calcium)	Max. 0.5 ppm
Cd (Cadmium)	Max. 0.02 ppm
Co (Cobalt)	Max. 0.005 ppm
Cr (Chromium)	Max. 0.005 ppm
Cu (Copper)	Max. 0.2 ppm
Fe (Iron)	Max. 0.1 ppm
K (Potassium)	Max. 0.1 ppm
Mg (Magnesium)	Max. 0.02 ppm
Mn (Manganese)	Max. 0.005 ppm
Mo (Molybdenum)	Max. 0.005 ppm
Na (Sodium)	Max. 0.1 ppm
Ni (Nickel)	Max. 0.02 ppm
Pb (Lead)	Max. 0.1 ppm
Sr (Strontium)	Max. 0.005 ppm
Zn (Zinc)	Max. 0.1 ppm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.