



Material	83645.320
Material description	Water
Grade	HiPerSolv CHROMANORM for HPLC LC-MS grade - suitable for UPLC/UHPLC instruments
CAS Number	7732-18-5
Molecular formula	H <sub>2</sub> O
Molecular mass	18.02

Characteristics	Specifications
Colouration	Max. 5 APHA
Conductivity (25°C) (at filling)	Max. 1 µS/cm
Evaporation residue	Max. 1 ppm
Al (Aluminium)	Max. 50 ppb
Ca (Calcium)	Max. 50 ppb
Fe (Iron)	Max. 50 ppb
K (Potassium)	Max. 50 ppb
Mg (Magnesium)	Max. 50 ppb
Na (Sodium)	Max. 100 ppb
Fluorescence (as quinine) (254/450 nm)	Max. 1 ppb
Fluorescence (as quinine) (365/450 nm)	Max. 0.5 ppb
Gradient (210 nm)	Max. 5 mAU
Gradient (220 nm)	Max. 2 mAU
Gradient (254 nm)	Max. 1 mAU
MS-ESI+ (as Reserpine)	Max. 2 ppb
MS-APCI+ (as Reserpine)	Max. 2 ppb
MS-ESI- (as 4-Nitrophenol)	Max. 20 ppb
MS-APCI- (as 4-Nitrophenol)	Max. 20 ppb
Colony count (Ph.Eur.) (at filling)	Max. 100 CFU/ml
TOC (at filling)	Max. 30 ppb

## Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare  
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;  
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.