



Model:  
**STB250 - 630-1576**

Typology:  
**ROUTINE STEREOMICROSCOPE**

Description:  
*Entry- level stereomicroscope for routine and industrial applications.*

<b>Illumination</b>	Double adjustable illuminator for incident and transmitted light fitted with two high-efficiency LED light sources. The angle of the incident illuminator is adjustable. Voltage: 110/240Vac, 50/60Hz, 1A ; Fuses: T1A 250V Maximum power consumption: 7W
<b>Focusing</b>	By means of a rack and pinion controlled by a pair of knobs placed on both sides of the microscope.
<b>Stage</b>	Fitted with a semi-transparent plastic disc for transmitted light with specimen clamps.
<b>Stand</b>	Fixed arm type with focusing mechanism.
<b>Head</b>	Binocular heads, 360° rotating, 45° inclined. Adjustable dioptic compensation on left eyepiece tube. Interpupillary distance adjustable between 51 and 75 mm.
<b>Eyepieces</b>	WF10x/20mm widefield eyepieces.
<b>Objectives</b>	Achromatic objectives 2X and 4X selectable through rotation. Working distance 80mm.
<b>Accessories</b>	Manual and dust cover included.