



Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

Revision date: 24.12.2017 Version: 7.0 Print date: 24.12.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name/designation: Sodium dihydrogen phosphate monohydrate AnalaR NORMAPUR®

a na lytical reagent

 Product No.:
 10245

 CAS No.:
 10049-21-5

 INDEX No.:
 000-000-00-0

REACH No.: Not yet communicated down the supply chain.

Other means of identification: no data available

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant i dentified uses: General chemical reagent

1.3 Details of the supplier of the safety data sheet

United Kingdom

VWR International Ltd.

Street Hunter Boulevard, Magna Park

Postal code/city Lutterworth, LE17 4XN

Telephone 0800 22 33 44
Telefax 01455 55 85 86
E-mail (competent person) SDS@vwr.com

Emergency telephone

Telephone +44 (0) 1270 502894 (CareChem24)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) No. 1272/2008 [CLP]

This substance is classified as not hazardous according to regulation (EC) No. 1272/2008 [CLP].





2.2 Label elements

2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]

According to EC directives or the corresponding national regulations the product does not have to be labelled.

Other hazards

not applicable

SECTION 3: Composition / information on ingredients

3.1 Substances

Substance name Sodium dihydrogen phosphate monohydrate

Molecular formula Na H2PO4·1H2O Molecular weight 137.99 g/mol CAS No. 10049-21-5

REACH registration No. Not yet communicated down the supply chain.

INDEX No. 000-000-00-0

SECTION 4: First aid measures

4.1 General information

When in doubt or if symptoms are observed, get medical advice. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

After inhalation

Remove casualty to freshair and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration. In case of respiratory tractirritation, consult a physician.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids a part and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

If a cci dentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

4.2 Most important symptoms and effects, both acute and delayed

no data available

4.3 Indication of any immediate medical attention and special treatment needed

no data available

4.4 Self-protection of the first aider

First aider: Pay attention to self-protection!





4.5 Information to physician

no data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

The product itself does not burn.

Co-ordinate fire-fighting measures to the fire surroundings.

Extinguishing media which must not be used for safety reasons

no restriction

5.2 Special hazards arising from the substance or mixture

In case offire may be liberated:

Phosphorus oxides

5.3 Advice for firefighters

 ${\tt DO\,NOT\,fight\,fire\,when\,fire\,re\,aches\,explosives.}$

Special protective equipment for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use waters pray jet to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Avoid generation of dust.

6.2 Environmental precautions

Do not allow to enter into surface water or drains.

6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Clean contaminated objects and areas thoroughly observing environmental regulations. Collect in closed and suitable containers for disposal.

6.4 Additional information

Clear spills immediately.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Avoid: Inhalation Avoid contact with skin and eyes. Use extractor hood (laboratory). If handled uncovered, a rrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means. Protect from moisture.





7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: 15-25°C

Storage class: 10-13

Keep container tightly closed and in a well-ventilated place.

7.3 Specific end use(s)

no data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

8.2.2 Personal protection equipment

We arsuitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn.

Eye/face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

Recommendation: VWR 111-0432

Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms: DIN EN 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

By short-term hand contact

Suitable material: NBR (Nitrile rubber)

Thickness of the glove material: 0,12 mm

Breakthrough time (maximum wearing time): > 480 min

Recommended glove articles: VWR 112-0998

By long-term hand contact

Suitable material: NBR (Nitrile rubber)

Thickness of the glove material: 0,38 mm
Breakthrough time (maximum wearing time): > 480 min

Recommended glove articles: VWR 112-3717 / 112-1381

Respiratory protection

Usually no personal respirative protection necessary.





Additional information

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

8.2.3 Environmental exposure controls

no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

(a) Appearance

Physical state: solid Colour: white

(b) Odour: no data a vailable (c) Odour threshold: no data a vailable

Safety relevant basic data

(d) pH: 4.1-4.5 (50 g/l; H2O; 20 °C)

(e) Melting point/freezing point: 100 °C

(f) Initial boiling point and boiling range:no data a vailable(g) Flash point:no data a vailable(h) Eva poration rate:no data a vailable(i) Flammability (solid, gas):not a pplicable

(j) Flammability or explosive limits

Lower explosion limit: no data a vailable
Upper explosion limit: no data a vailable
(k) Va pour pressure: no data a vailable
(l) Va pour density: no data a vailable
(m) Relative density: 2.04 g/cm³ (20 °C)

(n) Solubility(ies)

Water solubility (g/L): ~850 g/l (20 °C)
Soluble (g/L) in Ethanol: no data a vailable
(o) Partition coefficient: n-octanol/water: no data a vailable
(p) Auto-ignition temperature: no data a vailable
(q) Decomposition temperature: 110 °C (1013 hPa)

(r) Viscosity

Kine matic viscosity: no data a vailable
Dynamic viscosity: no data a vailable
(s) Explosive properties: not a pplicable
(t) Oxidising properties: not a pplicable

9.2 Other information

Bulk density:2.04 g/cm³ (20 °C)Refraction index:no data a vailableDissociation constant:no data a vailableSurface tension:no data a vailableHenry constant:no data a vailable





SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

no data available

10.6 Hazardous decomposition products

no data available

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:

LD50: > 8290 mg/kg - Rat - (RTECS)

Acute dermal toxicity:

LD50: < 7940 mg/kg - Rabbit - (IUCLID)

Acute inhalation toxicity:

no data available

Irritant and corrosive effects

Primary irritation to the skin:

not applicable

Irritation to eyes:

not applicable

Irritation to respiratory tract:

not applicable





Respiratory or skin sensitisation

In case of skin contact: not sensitising After inhalation: not sensitising

STOT-single exposure

 $not\,a\,p\,plicable$

STOT-repeated exposure

not applicable

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Carcinogenicity

No indication of human carcinogenicity.

Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

Reproductive toxicity

No indications of human reproductive toxicity exist.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:

no data available

Daphnia toxicity:

no data available

Algae toxicity:

no data available

Bacteria toxicity:

no data available

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data a vailable





12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

no data available

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

Dispose a ccording to local legislation. Consult the appropriate local waste disposal expert a bout waste disposal.

Waste code product: no data available

Appropriate disposal / Package

Dispose a ccording to local legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (ADR/RID)

No dangerous good in sense of this transport regulation.

Sea transport (IMDG)

No dangerous good in sense of this transport regulation.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code not relevant

Air transport (ICAO-TI / IATA-DGR)

No dangerous good in sense of this transport regulation.





SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

- Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, a mending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance) Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)
- Commission Regulation (EU) No 453/2010 of 20 May 2010 a mending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance) Commission Regulation (EU) 2015/830 of 28 May 2015 a mending Regulation (EC) No 1907/2006 of the European Parliament and
- of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

National regulations

no data available

Water hazard class (WGK): slightly hazardous to water (WGK 1)

15.2 Chemical Safety Assessment

notrelevant





SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygiensts

ADR - Europe an Agreement concerning the International Carriage of Dangerous Goods by Road

AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)

CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures

DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)

Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)

IATA-DGR - International Air Transport As sociation-Dangerous Goods Regulations

ICAO-TI - International Civil Aviation Organization - Technical Instructions

IMDG - International Maritime Code for Dangerous Goods

LTV - Long Term Value

NIOSH - National Institute for Occupational Safety and Health

OSHA - Occupational Safety & Health Administration

PBT - Persistent, Bioaccumulative and Toxic

 ${\tt RID-Regulation}\, concerning\, the\, International\, Carriage\, of\, Dangerous\, Goods\, by\, Rail$

STV - Short Term Value

SVHC - Substances of Very High Concern

vPvB - very Persistent, very Bioaccumulative

Additional information

Indication of changes: general update

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.