



Material	28195.238
Material description	Sodium wolframate dihydrate
Grade	AnalaR NORMAPUR
CAS Number	10213-10-2
Molecular formula	Na ₂ O ₄ W.2H ₂ O
Molecular mass	329.86

Characteristics	Specifications
Assay	Min. 99 %
Cl (Chloride)	Max. 30 ppm
SO ₄ (Sulphate)	Max. 100 ppm
Fe (Iron)	Max. 5 ppm
Mo (Molybdenum)	Max. 50 ppm
Pb (Lead)	Max. 10 ppm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Anja Vanhalle, Head of Laboratory - Haasrode
VWR International bvba; Geldenaaksebaan 464; BE-3001
Leuven; Belgium

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.