



Model:
SZB350 - 630-1578

Typology:
LABORATORY STEREOMICROSCOPE

Description:
Stereomicroscope for laboratory and industry applications.

Illumination	<p>Dual illuminator adjustable for transmitted and reflected light, intensity control with two knobs on the right side of the base.</p> <p>The illumination angle in reflected light is adjustable.</p> <p>Two halogen bulbs 12V/15W provided.</p> <p>Voltage: 110/240Vac, 50/60Hz, 1A ; Fuses: T1A 250V</p> <p>Max power required: 38W</p>
Focusing	By means of a rack and pinion controlled by a pair of knobs placed on both sides of the stereomicroscope.
Stage	<p>Fitted with a black disc and a white disc for contrast.</p> <p>Specimen clamps.</p> <p>Frosted glass disc for transmitted light.</p>
Stand	<p>Pillar stand height 25 cm.</p> <p>Base: 26x20x6h cm.</p> <p>Weight: 6 Kg</p>
Head	<p>Binocular rotating 360° and 45° inclined.</p> <p>Diopter adjustment on both eyepieces.</p> <p>Interpupillary adjustment 51-75 mm.</p>
Eyepieces	Widefield eyepieces WF10x/20 with field number 20.
Objectives	<p>Parfocal achromatic objective 1X</p> <p>Working distance: 100 mm</p> <p>Zoom range: 0,7x - 4,5x</p> <p>Zoom factor: 6,428:1</p>
Accessories	Instruction manual and dust cover included.