

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

Revision date: 29.12.2017

Version: 7.0

Print date: 29.12.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name/designation:	Nitrochromic reagent Reag. Ph. Eur. 1059100
Product No.:	87881
CAS No.:	not applicable
INDEX No.:	not applicable
REACH No.:	not applicable
Other means of identification:	no data available

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses:	Scientific research and development
---------------------------	-------------------------------------

1.3 Details of the supplier of the safety data sheet

United Kingdom

VWR International Ltd.

Street	Hunter Boulevard, Magna Park
Postal code/city	Lutterworth, LE17 4XN
Telephone	0800 22 33 44
Telefax	01455 55 85 86
E-mail (competent person)	SDS@vwr.com

Emergency telephone

Telephone	+44 (0) 1270 502894 (CareChem24)
-----------	----------------------------------

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazard classes and hazard categories	Hazard statements
Oxidising liquid, category 3	H272
Carcinogenicity, category 1B	H350
Germ cell mutagenicity, category 1B	H340
Reproductive toxicity, category 1B	H360Fd
Acute toxicity, category 3, inhalation	H331
Skin corrosion, category 1A	H314
Respiratory sensitization, category 1	H334
Skin sensitization, category 1	H317
Substance or mixture corrosive to metals, category 1	H290
Hazardous to the aquatic environment, chronic, category 3	H412

2.2 Label elements

2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms



Signal word: Danger

Hazard statements	
H272	May intensify fire; oxidiser.
H350	May cause cancer.
H340	May cause genetic defects.
H360Fd	Suspected of damaging fertility. Suspected of damaging the unborn child.
H331	Toxic if inhaled.
H314	Causes severe skin burns and eye damage.
H334	May cause allergy or asthma symptoms or breathing difficulties if inhaled.
H317	May cause an allergic skin reaction.
H290	May be corrosive to metals.
H412	Harmful to aquatic life with long lasting effects.



Precautionary statements	
P201	Obtain special instructions before use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P220	Keep/Store away from clothing/combustible materials.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P284	[In case of inadequate ventilation] wear respiratory protection.
P273	Avoid release to the environment.
P301+P330+P331	IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P302+P352	IF ON SKIN: Wash with plenty of water/...
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P310	IF exposed or concerned: Immediately call a POISON CENTER/doctor.

Other hazards

none

SECTION 3: Composition / information on ingredients

3.1 Substances

not applicable

3.2 Mixtures

Hazardous ingredients Classification according to Regulation (EC) No. 1272/2008 [CLP]

Substance name	Concentration	Product identifier	Hazard classes and hazard categories
Nitric acid	65 - 70%	CAS No.: 7697-37-2 EC No.: 231-714-2 REACH No.: 01-2119487297-23-XXXX	Ox. Liq. 3 - H272 Skin Corr. 1A - H314
Potassium dichromate	0.5 - 1%	CAS No.: 7778-50-9 EC No.: 231-906-6 REACH No.: 01-2119454792-32-XXXX	Ox. Sol. 2 - H272 Carc. 1B - H350 Muta. 1B - H340 Repr. 1B - H360FD Acute Tox. 2 - H330 Acute Tox. 3 - H301 STOT RE 1 - H372 Acute Tox. 4 - H312 Skin Corr. 1B - H314 STOT SE 3 - H335 Resp. Sens. 1 - H334 Skin Sens. 1 - H317 Aquatic Chronic 1 - H410

SECTION 4: First aid measures

4.1 General information

IF exposed: Immediately call a POISON CENTRE/doctor. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

After inhalation

Immediately call a POISON CENTRE/doctor. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. Immediate medical treatment required because corrosive injuries that are not treated are hard to cure.

After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

Immediately call a POISON CENTRE/doctor. Do NOT induce vomiting. Rinse mouth thoroughly with water. Give nothing to eat or drink.

4.2 Most important symptoms and effects, both acute and delayed

no data available

4.3 Indication of any immediate medical attention and special treatment needed

no data available

4.4 Self-protection of the first aider

First aider: Pay attention to self-protection!

4.5 Information to physician

no data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

The product itself does not burn.

May intensify fire; oxidiser.

Co-ordinate fire-fighting measures to the fire surroundings.

Extinguishing media which must not be used for safety reasons

no restriction

5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated:

Pyrolysis products, toxic

5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.

Special protective equipment for firefighters
Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Do not allow run-off from fire-fighting to enter drains or water courses.
Do not inhale explosion and combustion gases.
Use water spray jet to protect personnel and to cool endangered containers.
In case of fire: Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety.

6.2 Environmental precautions

Discharge into the environment must be avoided.

6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

6.4 Additional information

Clear spills immediately.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

All work processes must always be designed so that the following is as low as possible: Inhalation skin contact Eye contact Use extractor hood (laboratory). If handled uncovered, arrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: no data available
Storage class: no data available
Keep container tightly closed and in a well-ventilated place. Keep/Store only in original container.

7.3 Specific end use(s)

no data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredient (Designation)	Regulatory information	Country	Limit value type (country of origin)	Limit value	Remark
Nitric acid	2006/15/EC	EU	STV	2.6 mg/m ³ - 1 ppm	
Nitric acid	Gestis	UK	STV	2,6 mg/m ³ - 1 ppm	

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

8.2.2 Personal protection equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn.

Eye/face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

Recommendation: VWR 111-0432

Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms: DIN EN 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

By short-term hand contact

Suitable material:	Butyl caoutchouc (butyl rubber)/FKM (fluoro rubber)
Thickness of the glove material:	0,70 mm
Breakthrough time (maximum wearing time):	> 480 min
Recommended glove articles:	VWR 112-3819

By long-term hand contact

Suitable material:	Butyl caoutchouc (butyl rubber)/FKM (fluoro rubber)
Thickness of the glove material:	0,70 mm
Breakthrough time (maximum wearing time):	> 480 min
Recommended glove articles:	VWR 112-3819

Respiratory protection

Respiratory protection necessary at: aerosol or mist formation

Suitable respiratory protection apparatus:	Full-/half-/quarter-face masks (DIN EN 136/140)
Recommendation:	VWR 111-0206
Suitable material:	ABEK2P3
Recommendation:	VWR 111-0059

Additional information

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

8.2.3 Environmental exposure controls

no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	liquid
Colour:	no data available
(b) Odour:	no data available
(c) Odour threshold:	no data available

Safety relevant basic data

(d) pH:	no data available
(e) Melting point/freezing point:	no data available
(f) Initial boiling point and boiling range:	no data available
(g) Flash point:	no data available
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	not applicable
(j) Flammability or explosive limits	
Lower explosion limit:	no data available
Upper explosion limit:	no data available
(k) Vapour pressure:	no data available
(l) Vapour density:	no data available
(m) Relative density:	no data available
(n) Solubility(ies)	
Water solubility (g/L):	no data available
Soluble (g/L) in Ethanol:	no data available
(o) Partition coefficient: n-octanol/water:	no data available
(p) Auto-ignition temperature:	no data available
(q) Decomposition temperature:	no data available
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	no data available
(s) Explosive properties:	not applicable
(t) Oxidising properties:	May intensify fire; oxidiser.

9.2 Other information

Bulk density:	not applicable
Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry constant:	no data available

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

no data available

10.6 Hazardous decomposition products

no data available

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:

Nitric acid - LDLo: > 430 mg/kg - Human - (Sax)

Potassium dichromate - LD50: > 25 mg/kg - Rat - (RTECS)

Acute dermal toxicity:

Potassium dichromate - LD50: > 1170 mg/kg - Rat - (IUCLID)

Acute inhalation toxicity:

Nitric acid - LC50: 67 ppm - Rat - (National Library of Medicine ChemID Plus (NLM CIP))

Irritant and corrosive effects

Primary irritation to the skin:

Causes severe skin burns and eye damage.

Irritation to eyes:

Causes serious eye damage.

Irritation to respiratory tract:

not applicable

Respiratory or skin sensitisation

In case of skin contact: sensitising

After inhalation: sensitising

STOT-single exposure

not applicable

STOT-repeated exposure

not applicable

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**Carcinogenicity**

May cause cancer.

Germ cell mutagenicity

May cause genetic defects.

Reproductive toxicity

Suspected of damaging fertility. Suspected of damaging the unborn child.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:

Potassium dichromate - LC50: 51.1 mg/l (96 h)

Daphnia toxicity:

Potassium dichromate - EC50: 0.12 mg/l (48 h)

Potassium dichromate - LC50: 7.18 mg/l (48 h)

Algae toxicity:

Potassium dichromate - EC50: 0.61 mg/l (72 h)

Bacteria toxicity:

no data available

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available

12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

no data available

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (ADR/RID)

14.1	UN-No.:	3093
14.2	Proper Shipping Name:	CORROSIVE LIQUID, OXIDIZING, N.O.S. (NITRIC ACID/POTASSIUM DICHROMATE SOKUTION)
14.3	Class(es):	8 (5.1)
	Classification code:	CO1
	Hazard label(s):	8+5.1
14.4	Packing group:	II
14.5	Environmental hazards:	No
14.6	Special precautions for user:	
	Hazard identification number (Kemler No.):	85
	tunnel restriction code:	E
		(Passage forbidden through tunnels of category E.)

Sea transport (IMDG)

14.1	UN-No.:	3093
14.2	Proper Shipping Name:	CORROSIVE LIQUID, OXIDIZING, N.O.S. (NITRIC ACID/POTASSIUM DICHROMATE SOKUTION)
14.3	Class(es):	8 (5.1)
	Classification code:	
	Hazard label(s):	8+5.1

14.4	Packing group:	II
14.5	Environmental hazards:	No
	MARINE POLLUTANT:	No
14.6	Special precautions for user:	
	Segregation group:	-
	EmS-No.	F-A S-Q
14.7	Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	not relevant

Air transport (ICAO-TI / IATA-DGR)

14.1	UN-No.:	3093
14.2	Proper Shipping Name:	CORROSIVE LIQUID, OXIDIZING, N.O.S. (NITRIC ACID/POTASSIUM DICHROMATE SOLUTION)
14.3	Class(es):	8 (5.1)
	Classification code:	
	Hazard label(s):	8+5.1
14.4	Packing group:	II
14.5	Special precautions for user:	

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

- Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance)
- Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)
- Commission Regulation (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance)
- Commission Regulation (EU) 2015/830 of 28 May 2015 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

This mixture contains the following substances of very high concern (SVHC) which are subject to authorisation according to Annex XIV of REACH:

- Potassium dichromate (ED/30/2010 - SunsetDate: 21/09/2017)

National regulations

no data available

Water hazard class (WGK): no data available

15.2 Chemical Safety Assessment

no data available

SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists

ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road

AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)

CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures

DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)

Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)

IATA-DGR - International Air Transport Association-Dangerous Goods Regulations

ICAO-TI - International Civil Aviation Organization-Technical Instructions

IMDG - International Maritime Code for Dangerous Goods

LTV - Long Term Value

NIOSH - National Institute for Occupational Safety and Health

OSHA - Occupational Safety & Health Administration

PBT - Persistent, Bioaccumulative and Toxic

RID - Regulation concerning the International Carriage of Dangerous Goods by Rail

STV - Short Term Value

SVHC - Substances of Very High Concern

vPvB - very Persistent, very Bioaccumulative

Additional information

Indication of changes: general update

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.